

10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M

StarTech ID: *MXT101MMLP10*



The MXT101MMLP10 10-foot, Low Profile High Resolution Monitor VGA Extension Cable, is designed to provide the highest video quality available through VGA. This super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality High Resolution Monitor VGA Cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Replacement VGA/SVGA monitor cable
- Lightweight video cable for laptop
- Ideal for high resolution monitors (1024x768 and above)

Features

- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Technical Specifications

| | |
|---------------------------|--|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Type | PVC - Polyvinyl Chloride |
| Cable Shield Type | Aluminum-Mylar Foil with Braid |
| Connector A | 1 - VGA (15 pin; High Density D-Sub) Male |
| Connector B | 1 - VGA (15 pin; High Density D-Sub) Male |
| Color | Black |
| Wire Gauge | 32 AWG |
| Cable Length | 10 ft [3 m] |
| Shipping (Package) Weight | 0.4 lb [0.2 kg] |
| Included in Package | 1 - 10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M |

Certifications, Reports and Compatibility

