

6 ft Coax Low Profile High Resolution Monitor VGA Cable HD15 M/M
StarTech ID: MXT101MMLP6



StarTech.com's premium VGA Cables are designed to provide the highest video quality available through VGA.

This 6ft super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality VGA cable is backed by StarTech.com's Lifetime Warranty.

Applications and Solutions

- Extends VGA/SVGA monitor cable
- Lightweight video cable for laptop

Features

- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 100
- Shipping (Package) Weight: 0.27 lb [0.12 kg]
- Cable Length: 6 ft [1.83 m]
- Connector A: 1 - 15 pin High Density D-Sub (VGA) Male
- Connector B: 1 - 15 pin High Density D-Sub (VGA) Male

