

6 ft Coax Low Profile High Resolution Monitor VGA Cable HD15 M/M

StarTech ID: MXT101MMLP6



StarTech.com's premium VGA Cables are designed to provide the highest video quality available through VGA.

This 6ft super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality VGA cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Extends VGA/SVGA monitor cable
- Lightweight video cable for laptop

Features

- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Technical Specifications

Warranty	Lifetime
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Color	Black
Cable Length	6 ft [1.8 m]
Shipping (Package) Weight	0.3 lb [0.1 kg]

Certifications, Reports and Compatibility

