

Aluminum Dual Fan Laptop Cooler with USB Hub and Card Reader

StarTech ID: NBCOOLERPRO



This high quality laptop cooler offers professional-grade notebook cooling, helping to keep your laptop cooler than typical operating temperatures would permit, in turn optimizing system performance.

An innovative, space-saving solution, the laptop cooler also functions as a docking station for flash cards and additional USB 2.0 devices.

The laptop cooler features specialized aluminum construction and integrated dual high performance fans combined to deliver effective ventilation and maximized heat dissipation - reducing underside temperature to keep your laptop running cool. The laptop cooler also houses a built-in multi-card reader/writer to support most of today's popular flash card formats (12 types in all) as well as an additional 2 port USB high-speed hub to expand your access to additional USB devices.

The cooler includes an optional 5VDC power supply that gives you the option to power the cooling fans with a USB connection to the host laptop, or externally through a nearby power outlet - a sensible solution for preserving your laptop battery charge time.

Designed to provide a durable mobile computing operating platform, the laptop cooler is backed by StarTech.com's 2-year warranty.

Applications

- Ideal for desktop laptops where desktop space and system expandability is limited
- Provides convenience to mobile users by expanding their functionality away from office and minimizing the number of peripherals they transport

Features

- Card Reader/Writer supports most of popular types of flash cards - Secure Digital (SD), Multimedia (MMC), SmartMedia (SM), Memory Stick (MS), Memory Stick Pro (MSP) and more.
- Two built-in 70x70x15 mm cooling fans
- Fan On/Off switch
- Compliant with majority of laptops and notebook computers
- Includes optional power supply (5VDC)

Technical Specifications

Warranty	2 Years
Air Flow Rate	12.5 CFM
Noise Level	<16.9 dBA
General Specifications	1 USB mini B Female
General Specifications	1500 RPM +/- 10%
General Specifications	2 USB A Female
General Specifications	40K Hours at 25 degrees C
General Specifications	5V DC / 1 Amp
General Specifications	950 g
General Specifications	MMC, MMC 4.0, MMC High Speed, MMC Mobile, MMC plus 200X, RS MMC, RS MMC 4.0, RS MMC DV, RS MMC High Speed
General Specifications	MS Pro, MS Pro MG Hi-Speed, MS Pro MG Extreme, MS Pro MG Extreme III, MS Pro Duo, MS pro Duo MG Ultra II, MS Pro Duo MG Hi-Speed, MS Pro MG Ultra II, MS Pro Magic Gate, MS Pro Duo Magic Gate
General Specifications	MS, MS Duo, S Duo MG Hi-Speed, MS-Magic Gate, MS Duo Magic Gate, MS Memory Selection Function, MS ROM
General Specifications	Power Adapter is included
General Specifications	SD, SD Pro, SD Elite Pro, SD Ultra, SD Ultra II, SD Extreme, SD Extreme III, SD High Speed 150X
General Specifications	Smart Media, SMC, xD, xD M type
Color	Silver
Enclosure Type	Aluminum
Product Length	10.4 in [265 mm]
Product Width	12.6 in [320 mm]
Product Height	1.2 in [30 mm]
Product	2.2 lb [1 kg]

Weight
Shipping (Package) Weight 3.3 lb [1.5 kg]

Certifications, Reports and Compatibility

