

### 3 Port PCI 1394a FireWire Adapter Card with Digital Video Editing Kit

StarTech ID: *PCI1394\_2*



This 3 Port PCI Low Profile 1394a FireWire Adapter Card turns a motherboard PCI slot into two external IEEE 1394a FireWire slots (1x6-pin, 1x4-pin), and provides an internal (6-pin) FireWire port that can be used in place of the external 6-pin connector - a cost-effective solution that lets you connect any FireWire 400 device to your desktop computer.

Compatible with either Mac or PC computers, the 1394a FireWire card provides a practical solution for connecting iPods, MP3 players, portable drives, digital camcorders and more to your computer and supports hot-swappable connectivity, allowing you to plug, unplug, and swap your FireWire peripherals with ease.

A versatile FireWire video editing solution, the adapter card can be installed in a PCI 5V or PCI-x 3.3V slot, and includes a copy of ULEAD's VideoStudio SE Basic video editing software (Windows only), making it easy to capture and edit video from your digital video camcorder.

#### Applications

- iPods/MP3 players
- Portable hard drives
- External CDR-CDRW drives
- DVD drives
- Digital cameras
- Digital camcorders
- Scanners
- Printers

## Features

- Includes everything needed to edit your own home movies, add scene transitions and other effects with the included ULEAD® VideoStudio® SE software
- High speed data transfer rates of up to 400 Mbits/sec.
- Hot swap capabilities allows you to connect or disconnect devices without turning off your computer
- An internal connector allows for the easy connection of internal FireWire® peripherals

**Technical Specifications**

Warranty	Lifetime
Ports	3
Interface	FireWire 400 (1394a)
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Industry Standards	IEEE 1394
Industry Standards	IEEE 1394a
Industry Standards	OHCI
Industry Standards	PCI 2.1
Chipset ID	VIA - VT6307
Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V; 32-bit) Male
Internal Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
External Ports	1 - Firewire 400 (4 pin; IEEE 1394a) Female
External Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
Maximum Data Transfer Rate	400 Mbps
OS Compatibility	Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit), Mac OS 8.6 and up, and Linux
Microsoft WHQL Certified	Yes
Product Length	4.7 in [12 cm]
Product Height	2.4 in [6.1 cm]
System and Cable Requirements	Unused PCI slot
<b>Note</b>	The internal port and the top external port share the same connection, meaning that only one of these two ports can be used at a time. Configured with standard bracket and low profile bracket included
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in	1 - 2 Port Firewire Card

Package	
Included in Package	1 - Firewire Cable
Included in Package	1 - Low Profile Bracket
Included in Package	1 - Standard Bracket
Included in Package	1 - Video Editing Software Kit
Included in Package	1 - Instruction Manual

**Certifications, Reports and Compatibility**

