

1 Port Low Profile PCI Parallel Adapter Card

StarTech ID: PCI1P_LP



The PCI1P_LP 1 Port Low Profile PCI Parallel Adapter Card adds one IEEE 1284 port to your small form factor PC, with data transfer speeds of up to 1.5 Mbps – up to 3 times faster than on-board parallel ports. The adapter card features a low profile design that is suited to small form factor computer cases, while including a full height bracket to adapt to any installation.

Installation is a breeze with plug and play support and drivers for Windows® 7, Vista, XP, ME, 2000, 98, 95, NT4, DOS® and Linux®. IRQ sharing and hot swapping capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications and Solutions

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Compatible with low profile systems
- Supports EPP, ECP, SPP and BPP
- IRQ sharing eliminates conflicts between multiple cards
- Data transfer rates of up to 1.5 Mbps
- Easy plug and play installation
- Installation scripts available for Linux RedHat 7.2, SuSE 7.3 and Mandrake 8.2

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI (5 Volt)
- Chipset ID: MosChip NM9805
- Connector Types: 1 - DB25 Female
- Maximum Data Transfer Rate: 1.5 Mbps
- Carton Quantity: 50
- Industry Standards: PCI 2.1
- Industry Standards: EPP
- Industry Standards: ECP
- Industry Standards: SPP
- Industry Standards: BPP
- Shipping (Package) Weight: 0.29 lb [0.13 kg]
- OS Compatibility: DOS, Windows 95/ 98/ ME/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux

