

## 1 Port PCI Dual Voltage WHQL Approved DB9 Serial Adapter Card with Legacy Port Remap Function

StarTech ID: PCI1S650DV



Get more out of your serial devices! StarTech.com's PCI1S650DV is a 1 port dual voltage serial card with WHQL certified drivers. Connecting legacy serial devices is no longer an issue as this card will remap to the necessary I/O address required by your device.

Great for connecting any new or old serial peripheral, with data transfer rates of up to 920 Kbits/sec. Dual Voltage compatibility allows you to install into a PCI or PCI-X slot. Perfect for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system. Installation is a breeze with support for Windows® Vista, XP, Server 2003, 2000, ME, 98, 95, NT4, 3.1, DOS® and Linux®. Guarantee convenient, hassle-free connections. Backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support.

### Applications

- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Security (UPS control, access key panels, video cameras, card readers, modems)
- Casino (video lottery terminals, slot machines)
- Consumer (modems, PDAs, digital cameras, printers)
- Environmental Control (lighting, temperature, clocks)
- Healthcare (patient monitoring equipment, nurses' stations, modems)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- ISDN Networking

**Features**

- Legacy port remap function allows you to re-assign I/O addresses and IRQ's for your legacy devices.
- Dual voltage card supports both 64-bit(3.3V) and 32-bit(5V) PCI
- High speed serial data transfers up to 920Kbps (depending on Operating System)
- 128K transmit/receive FIFO buffer helps improve overall system performance
- IRQ sharing eliminates IRQ conflicts
- Microsoft WHQL certified drivers

**Technical Specifications**

Warranty	Lifetime
Ports	1
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Integrated on Card
Chipset ID	Sunix - SUN1889
Connector Type(s)	1 - DB-9 (9 pin; D-Sub) Male
Serial Protocol	RS-232
Chipset	Sunix SUN1889
Compatible OS	DOS, Windows 95, 98, ME, NT; Windows XP (32-bit, 64-bit), Windows Vista (32-bit, 64-bit), Linux
Data Transfer Rate (max)	920 Kbits
Legacy Port Remap Addressing	3F8, 3E8, 2F8, 2E8
Supported Operating Systems for Remap Function	Microsoft DOS and Win9x/ME/NT 4.0
Microsoft WHQL Certified	Yes
Product Length	4.7 in [120 mm]
Product Width	2 in [5.2 cm]
Product Weight	1.5 oz [42 g]
Operating Temperature	0-57
Storage Temperature	20-85
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - 1 Port PCI Serial I/O card
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

