

## 4 Port USB 2.0 3 Port IEEE 1394a PCI USB Firewire Combo Adapter Card

StarTech ID: *PCI3UV22F*



This USB and FireWire slot saver PCI card can be installed in an available PCI slot to provide three external USB 2.0 ports, one internal USB port, two external 6-pin IEEE 1394a FireWire ports and one internal FireWire (6-pin, 1394a) port.

A cost-effective solution, the USB/FireWire slot saver PCI card lets you connect FireWire or USB peripherals (e.g CD-RW/DVD-ROMs, external hard drives, video cameras, etc.), while taking up only one PCI expansion slot on the computer, in turn saving space in the computer for further card installations.

Supporting full high-speed USB (up to 480Mbps) and FireWire 400 (400Mbps) data transfer speeds, the adapter card lets you get the most from your USB or FireWire peripherals, ensuring seamless functionality with internally or externally connected peripherals.

Plus, the adapter is backward compatible with USB 1.1 devices, ensuring that even older USB peripherals can be connected.

Designed for long-lasting durability, the USB 2.0/FireWire 400 slot saver card is backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support.

### Applications

- Connect to a wide range of USB 2.0/1.1 and IEEE-1394 FireWire® devices including CD-RW/DVD-ROMs, removable hard drives, video cameras, hubs, digital camcorders/cameras and MP3 players/iPods

## Features

- Three external (plus one internal) USB 2.0 ports with data transfer rates up to 480 Mbits/sec
- Two external (plus one internal) IEEE-1394 FireWire® ports with data transfer rates up to 400 Mbits/sec
- Hot swap capabilities let you connect peripherals without rebooting
- Compliant with PCI specification 2.2
- Backward compatible with USB 1.1 devices
- Installs easily into a single PCI slot

Technical Specifications

Warranty	Lifetime
Ports	3
Interface	FireWire 400 (1394a)
Interface	USB 2.0
Bus Type	PCI / PCI-X (5 / 3.3V)
Chipset ID	VIA - VT6214L & VT6306
Chipset ID	VIA VT6306
Connector Type(s)	3 - Firewire 400 (6 pin; IEEE 1394a) Female
Connector Type(s)	4 - USB A (4 pin) Female
Maximum Data Transfer Rate	480 Mbits/Sec
General Specifications	
General Specifications	1 x 6 pin 1394A
General Specifications	1 x USB Type A Female
General Specifications	1394 & 1394A
General Specifications	2 x 6 pin 1394A
General Specifications	3 x USB Type A Female
General Specifications	EHCI and OHCI Compliant
General Specifications	PC - Intel Pentium 2 at 400MHz or faster, Intel Celeron at 900MHz or faster, AMD Athlon of any speed
General Specifications	Mac - G3 original processor or faster
General Specifications	PCI
General Specifications	Up to 12 Mbits/sec
General Specifications	Up to 400 Mbits/sec
General Specifications	Up to 480 Mbps

General Specifications	Version 2.2
OS Compatibility	Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.2.6 or OS 10.2.8
Microsoft WHQL Certified	Yes
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - PCI USB 2.0 and 1394a Combo Card
Included in Package	1 - Instruction Manual

**Certifications, Reports and Compatibility**

