

4 Port PCI Dual Voltage WHQL Approved Serial Adapter Card with Legacy Port Remap Function

StarTech ID: PCI4S650DV



Get more out of your serial devices! StarTech.com's PCI4S650DV is a 4 port dual voltage serial card with WHQL certified drivers. Connecting legacy serial devices is no longer an issue as this card will remap to the necessary I/O address required by your device.

Great for connecting any new or old serial peripheral, with data transfer rates of up to 920 Kbits/sec. Dual Voltage compatibility allows you to install into a PCI or PCI-X slot. Perfect for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system. Installation is a breeze with support for Windows® Vista, XP, Server 2003, 2000, ME, 98, NT4, 3.1, DOS® and Linux®. Guarantee convenient, hassle-free connections. Backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support.

Applications

- Casino (video lottery terminals, slot machines)
- Consumer (modems, PDAs, digital cameras, printers)
- Environmental Control (lighting, temperature, clocks)
- Healthcare (patient monitoring equipment, nurses' stations, modems)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- ISDN Networking
- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Security (UPS control, access key panels, video cameras, card readers, modems)

Features

- Legacy port remap function allows you to re-assign I/O addresses and IRQ's for your legacy devices.
- 128K transmit/receive FIFO buffer helps improve overall system performance
- Dual voltage card supports both 64-bit(3.3V) and 32-bit(5V) PCI
- High speed serial data transfers up to 920Kbps (depending on Operating System)
- IRQ sharing eliminates IRQ conflicts
- Microsoft WHQL certified drivers

Technical Specifications

Warranty	Lifetime
Chipset ID	Sunix - SUN1889
Ports	4
Bus Type	PCI/PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Dongle (Included)
Connector Type(s)	1 - DB-37 (37 pin; D-Sub) Female
Max Baud Rate	921.6 Kbps
Serial Protocol	RS-232
Legacy Port Remap Addressing	3F8, 3E8, 2F8, 2E8
OS Compatibility	Windows® Vista (32-bit, 64-bit), XP (32/64), ME, NT, 98, 95, DOS Linux
Microsoft WHQL Certified	Yes
Product Length	4.7 in [120 mm]
Product Width	3.1 in [8 cm]
Product Weight	2.5 oz [70 g]
Operating Temperature	0-57
Storage Temperature	20-85
Note	Legacy remap function supported on DOS and Win9x/ME/NT 4.0
Shipping (Package) Weight	0.9 lb [0.4 kg]
Included in Package	1 - 4 Port PCI/PCI-X Serial I/O Card
Included in Package	1 - DB37 to 4 port DB9 cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

