

Features

- 7.1 Surround Sound Audio out
- Support 48/44.1 KHz sampling rate for both playback and recording
- Supports the latest Dolby® Digital EX and DTS ES 7.1 CH DVD soundtrack playback
- DirectSound™ 3 HW acceleration
- Supports PCI Version 2.2 with ACPI and PMI support
- Supports PnP installation with Windows WDM drivers
- Two internal auxiliary inputs
- Supports Full-Duplex operation; 8 outbound stream and 2 simultaneous input streams

Technical Specifications

| | |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Warranty | 2 Years |
| Bus Type | PCI (5 Volt) |
| Card Type | Standard Profile |
| Chipset ID | VIA - Tremor VT1723 |
| Connector Type(s) | 1 - PCI (5V; 32-bit) Male |
| Internal Ports | 2 - MPC2 (4 pin; Audio) Male |
| External Ports | 1 - Digital Coax Audio (RCA) Female |
| External Ports | 6 - 3.5 mm Mini-Jack (3 Position) Female |
| Audio Specifications | Input and Output Connections:Line In, Microphone, Front Out, Rear Out, Surround Out, Sub/Center Out, and S/PDIF (Digital) out |
| Full Duplex Support | Yes |
| OS Compatibility | Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64-bit)/ 7(32/64bit) |
| Microsoft WHQL Certified | Yes |
| Product Length | 4.8 in [121 mm] |
| Product Width | 3.1 in [80 mm] |
| Product Height | 0.7 in [18 mm] |
| Product Weight | 2.1 oz [59 g] |
| Operating Temperature | 205/8/2012eg;C to 505/8/2012eg;C (685/8/2012eg;F to 1225/8/2012eg;F) |
| Storage Temperature | 05/8/2012eg;C to 705/8/2012eg;C (325/8/2012eg;F to 1585/8/2012eg;F) |
| Humidity | 5 to 85% RH |
| Shipping (Package) Weight | 0.8 lb [0.3 kg] |
| Included in Package | 1 - 7.1 Surround Sound PCI Card |
| Included in Package | 1 - Driver CD |
| Included in Package | 1 - Instruction Manual |

Certifications, Reports and Compatibility

