

3 Port USB 2.0 and 3 Port IEEE-1394b FireWire Slot Saver PCI Express Card

StarTech ID: PEX3U3F800



Expand your connectivity and save PCI slots with StarTech.com's USB 2.0/FireWire® 800 slot saver PCI card. Three USB 2.0 ports (two external) and three FireWire® IEEE 1394b ports (two external), let you connect high-end peripherals like CD-RW/DVD-ROMs, removable hard drives, video cameras, hubs, digital camcorders/cameras, MP3 players and more.

The USB 2.0 ports provide up to 480 Mbits/sec of data transfer and are backwards compatible with your older USB 1.1 devices. The FireWire® ports provide up to 800 Mbits/sec of data transfer. Backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support. Get the best of USB 2.0 and FireWire® 1394b in a single card with the PEX3U3F800.

Applications

- Connect to a wide range of USB 2.0/1.1 and IEEE-1394 FireWire® devices including CD-RW/DVD-ROMs, removable hard drives, video cameras, hubs, digital camcorders/cameras and MP3 players/iPods

Features

- Backward compatible with USB 1.1 devices
- Compliant with PCI specification 2.2
- Hot swap capabilities let you connect peripherals without rebooting
- Installs easily into a single PCI slot
- Three external (plus one internal) USB 2.0 ports with data transfer rates up to 480 Mbits/sec
- Two external (plus one internal) IEEE-1394 FireWire® ports with data transfer rates up to 400 Mbits/sec

Technical Specifications

Warranty	Lifetime
Bus Type	PCI Express
Chipset ID	NEC 0720101GJ
Chipset ID	Renesas/NEC - 0720101GJ
Connector Type(s)	3 - Firewire 800 (9 pin; IEEE 1394b) Female
Connector Type(s)	4 - USB A (4 pin) Female
Maximum Data Transfer Rate	800000000 Kbits/Sec
General Specifications	
General Specifications	1 x 4 pin USB Type A
General Specifications	1 x 9 pin 1394B
General Specifications	1394A & 1394B
General Specifications	2 x 9 pin 1394B
General Specifications	3 x 4 pin USB Type A
General Specifications	EHCI and OHCI Compliant
General Specifications	Linux, Windows 2000/XP/Server 2003/Vista MAC G5 and up
General Specifications	PCI Express
General Specifications	Up to 12 Mbits/sec
General Specifications	Up to 480 Mbits/sec
General Specifications	Up to 800 Mbits/sec
Microsoft WHQL Certified	Yes
Shipping (Package) Weight	0.4 lb [0.2 kg]

Certifications, Reports and Compatibility

