

***D* 1 Port 10-Mbps Parallel Print Server**

StarTech ID: PM1000IPNDS



Save precious time and space with the compact StarTech.com 1-Port 10-Mbps Print Server. No need for a printer-dedicated computer, this adapter will have your printer connected to your Network in about 5 minutes. Included in the package is installation management software to customize each server port to the printers' advanced features and abilities. The fast DMA driven parallel ports eliminate bottlenecks while the device features multiprotocol support for both Novell IPX/SPX and TCP/IP (including fixed IP address and DHCP).

Features

- Allows you to quickly and easily add printers to your network - can be installed in as little as 5 minutes.
- Compact size.
- Fast DMA driven parallel ports eliminate bottlenecks.
- Features flash EEPROM for quick and easy upgrades.
- Includes installation management software to customize each server port to the printers' advanced features and abilities.
- Multiprotocol support for both Novell IPX/SPX and TCP/IP (including fixed IP address and DHCP).

Technical Specifications

- Warranty: 2 Year warranty
- Color: Beige
- Connector Types: 1 - Centronics 36 Male
- Connector Types: 1 - RJ45 Female
- Connector Types: 1 - BNC Female
- Enclosure Type: Plastic
- Number of Ports: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 1A
- Power Adapter - DC Voltage: 6V
- Center Tip Polarity: Positive
- Shipping (Package) Weight: 1.52 lb [0.69 kg]
- Ports: (1) Parallel (Centronics 36 Male)
- AC Input: 120V 60Hz 15W