

***D* 1 Port 10-Mbps Parallel Print Server**

StarTech ID: PM1000IPNDS



Save precious time and space with the compact StarTech.com 1-Port 10-Mbps Print Server. No need for a printer-dedicated computer, this adapter will have your printer connected to your Network in about 5 minutes. Included in the package is installation management software to customize each server port to the printers' advanced features and abilities. The fast DMA driven parallel ports eliminate bottlenecks while the device features multiprotocol support for both Novell IPX/SPX and TCP/IP (including fixed IP address and DHCP).

Features

- Allows you to quickly and easily add printers to your network - can be installed in as little as 5 minutes.
- Includes installation management software to customize each server port to the printers' advanced features and abilities.
- Features flash EEPROM for quick and easy upgrades.
- Fast DMA driven parallel ports eliminate bottlenecks.
- Multiprotocol support for both Novell IPX/SPX and TCP/IP (including fixed IP address and DHCP).
- Compact size.

Technical Specifications

Warranty	2 Years
Ports	1
External Ports	1 - BNC (RF Coax) Female
External Ports	1 - Centronics (36 pin) Male
External Ports	1 - RJ-45 Female
General Specifications	(1) Parallel (Centronics 36 Male)
General Specifications	120V 60Hz 15W
Color	Beige
Enclosure Type	Plastic
Power Adapter Included	Yes
Center Tip Polarity	Positive
Shipping (Package) Weight	1.5 lb [0.7 kg]
Included in Package	1 - ETHERNET PRINT SERVER
Included in Package	1 - BNC CONNECTOR
Included in Package	1 - POWER ADAPTER
Included in Package	1 - CD DRIVER
Included in Package	1 - INSTRUCTION MANUAL