

1 Port 10/100 Mbps Parallel Network Print Server

StarTech ID: PM1115P



This 10/100 Mbps Print Server lets you connect a Parallel printer to your Fast Ethernet (10/100Mbps) network, allowing you to share the printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The parallel print server can be installed in minutes and features remote web-based management for simple configuration. The print server features a small footprint design that saves valuable desk space, and can be connected directly into the parallel printer Centronics port and connected to a Fast Ethernet network using standard network cable (RJ45 terminated).

Providing dependable parallel printer sharing, this 10/100Mbps Print Server is backed by StarTech.com's 2-year warranty.

Applications

- Connects your Ethernet network to one Parallel printer
- PM1115P offers network printing solution for home, small office, educational & government institutions and any other environments that require printer sharing

Features

- Compact and light weight print server only weighs 2.4 ounces
- Compliant with IEEE 1284, IEEE 802.3 & IEEE 802.3u standards
- Configurable using a Web based browser or a Windows based configuration
- Connects directly to the Centronics port of your printer
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

Technical Specifications

Warranty	2 Years
Ports	1
External Ports	1 - Centronics (36 pin) Male
External Ports	1 - RJ-45 Female
Remote Management Ability	Yes
Supported Protocols	AppleTalk
Supported Protocols	IPX/SPX
Supported Protocols	NetBEUI
Supported Protocols	SMNP
Supported Protocols	TCP/IP
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8(32/64-bit) Mac OS X and up Linux
Color	Beige
Enclosure Type	Plastic
Product Length	2.2 in [55 mm]
Product Width	2 in [50 mm]
Product Height	0.9 in [22 mm]
Product Weight	2.4 oz [67 g]
LED Indicators	1 - Activity
LED Indicators	1 - LAN
LED Indicators	1 - Status
Power Adapter Included	Yes
Input Voltage	115 AC
Output Voltage	7.5 DC
Output Current	2A
Center Tip Polarity	Positive
System and Cable Requirements	Ethernet network cable not included
Shipping (Package) Weight	1.1 lb [0.5 kg]
Included in Package	1 - Parallel Print Server
Included in Package	1 - Power Adapter (NA)

- Included in Package 1 - Driver CD
- Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

