

10/100 Mbps USB Print Server
StarTech ID: PM1115U



This USB 10/100 Mbps Print Server lets you share one printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The Print server (PM1115U) does not require a dedicated print server PC, so you can position the printer anywhere on your network, while avoiding the performance bottleneck you would experience with an always-on PC acting as the print server.

PM1115U features straightforward installation wizards and remote web-based management, simplifying the print server's installation and use. The palm-sized, lightweight print server plugs directly into your printer's USB port and needs only an RJ-45 networking cable to connect it to the rest of your network.

Compatible with most major operating systems, the 1 Port USB 10/100 Mbps Print Server is the perfect USB printer solution for home or small office networks.

Applications and Solutions

- Connects your Ethernet network to one USB printer
- PM1115U offers network printing solution for home, small office, educational & government institutions and any other environments that require printer sharing

Features

- Compact and light weight USB print server only weighs 1.6 ounces
- Compliant with USB 2.0
- Configurable using a web based browser or a windows based configuration
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 USB printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

Technical Specifications

- Warranty: 2 Year warranty
- Color: Beige
- Connector Types: 1 - RJ45 Female
- Connector Types: 1 - USB A Female
- Enclosure Type: Plastic
- Product Height: 0.79 in [2 cm]
- LED Indicators: 1 - Status
- LED Indicators: 1 - LAN Connectivity
- LED Indicators: 1 - Activity
- Product Length: 2.95 in [7.5 cm]
- Maximum Data Transfer Rate: 100000 Mbits/Sec
- Number of Ports: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 500 mA
- Power Adapter - DC Voltage: 7.5V DC
- Center Tip Polarity: Positive
- Supported Protocols: AppleTalk
- Supported Protocols: IPX
- Supported Protocols: LPR
- Supported Protocols: NetBEUI
- Supported Protocols: SNMP

- Supported Protocols: TCP/IP
- Carton Quantity: 20
- Remote Management Ability: Yes
- Shipping (Package) Weight: 1.13 lb [0.51 kg]
- Product Weight: 1.59 oz [45 g]
- Product Width: 2.17 in [5.5 cm]

