

10/100 Mbps USB Print Server

StarTech ID: PM1115U



This USB 10/100 Mbps Print Server lets you share one printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The Print server (PM1115U) does not require a dedicated print server PC, so you can position the printer anywhere on your network, while avoiding the performance bottleneck you would experience with an always-on PC acting as the print server.

PM1115U features straightforward installation wizards and remote web-based management, simplifying the print server's installation and use. The palm-sized, lightweight print server plugs directly into your printer's USB port and needs only an RJ-45 networking cable to connect it to the rest of your network.

Compatible with most major operating systems, the 1 Port USB 10/100 Mbps Print Server is the perfect USB printer solution for home or small office networks.

Applications

- Connects your Ethernet network to one USB printer
- PM1115U offers network printing solution for home, small office, educational & government institutions and any other environments that require printer sharing

Features

- Compact and light weight USB print server only weighs 1.6 ounces
- Compliant with USB 2.0
- Configurable using a web based browser or a windows based configuration
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 USB printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

Technical Specifications

Warranty	2 Years
Ports	1
External Ports	1 - RJ-45 Female
External Ports	1 - USB A (4 pin) Female
Maximum Data Transfer Rate	100 Mbps
Remote Management Ability	Yes
Supported Protocols	AppleTalk
Supported Protocols	IPX
Supported Protocols	LPR
Supported Protocols	NetBEUI
Supported Protocols	SNMP
Supported Protocols	TCP/IP
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit)/ Server 2008 R2, Linux, and Mac OS X and up
Color	Beige
Enclosure Type	Plastic
Product Length	3 in [7.5 cm]
Product Width	2.2 in [5.5 cm]
Product Height	0.8 in [2 cm]
Product Weight	1.6 oz [45 g]
LED Indicators	1 - Activity
LED Indicators	1 - LAN Connectivity
LED Indicators	1 - Status
Power Adapter Included	Yes
Output Voltage	7.5 DC
Output Current	0.5A
Center Tip Polarity	Positive
System and Cable Requirements	USB printer cable not included
Shipping (Package) Weight	1.1 lb [0.5 kg]
Included in Package	1 - USB Print Server

Included in Package 1 - Power Adapter (NA)

Included in Package 1 - Driver CD

Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

