

## 10 ft 24V to 2x4 PoweredUSB Cable

StarTech ID: PUSB2X424V10



This 10ft 24V to 2x4 Powered USB Cable features one 24v Powered USB Connector as well as one 2x4 Pin Connector, providing a durable 10ft connection for Powered USB devices.

Providing both USB data and USB device power through a single cable, Powered USB technology is emerging as the industry standard in a broad range of environments including retail POS, industrial, security and medical, based on true plug-and-play connectivity.

StarTech.com's versatile line of powered USB cables offers the high quality design and construction needed to usher in a new generation of USB connectivity, providing superb grounding and protection for all components as well as protection against the normal wear and tear that can result from repeated insertions and removals. This 24V to 2x4 Powered USB Cable is backed by StarTech.com's Lifetime Warranty.

### Features

- Compatible with USB 1.1/2.0 standards and Powered USB peripheral devices
- Eliminating external power supply needs for USB peripheral devices such as receipt printers, signature capture devices and bar-code scanners
- Has a unique cable locking feature
- Plug and Play
- Reduces clutter and frees up space

**Technical Specifications**

Warranty	Lifetime
Connector A	1 - PoweredUSB 24V (8 pin; Host Side) Male
Connector B	1 - PoweredUSB 2x4 (8 pin; Remote Side) Female
Cable Length	10 ft [3 m]
Product Length	10 ft [3 m]
Shipping (Package) Weight	0.6 lb [0.3 kg]

**Certifications, Reports and Compatibility**

