


## 2 Port 12V 24V PoweredUSB Adapter Card - USB PlusPower

StarTech ID: PUSBADAP



Offering true Powered USB (USB PlusPower) versatility, this 2 port 12V/24V Powered USB Adapter Card acts as the daughter board component to StarTech.com's [3 Port PCI 12V Powered USB Card \(PCI312PUSB\)](#), expanding the number of Powered USB ports provided for a total of five Powered USB ports.

Alternatively, the adapter card does not require a direct connection to the motherboard PCI local bus, letting you install the card as a standalone 2 port Powered USB card.

### Applications and Solutions

- External CD-ROM, DVD drive and Hard drives that require more than 500mA current
- Gaming industry (joysticks with feedback mechanisms)
- Mobile Computing (delivery services, overland transportation)
- Point-of-Care (POC)
- Point-of-Sale (POS)

## Features

- Can connect to a Powered USB Main Board or a mother board of a PC using an extension cable
- Doesn't require a PCI slot
- Provides 2 powered USB ports that supply 24V and 12V power.
- Provides 3A of current for each port
- 4 pin Din connector acts as an optional external 24V AC adapter
- Backwards compatible with USB 2.0 and 1.1

## Technical Specifications

- Warranty: Lifetime warranty
- Product Length: 4.72 in [120 mm]
- Carton Quantity: 50
- Shipping (Package) Weight: 0.44 lb [0.2 kg]
- Product Weight: 7.06 oz [200 g]
- Product Width: 2.63 in [66.7 mm]
- Operates in two separate modes:
- General Specifications: Connect from the internal USB connector to the main board on the Powered USB card
- General Specifications: Stand Alone Mode connects via internal USB connect to the Mother Board of the PC
- Connectors:
- General Specifications: 1x 24V Power USB Connector
- General Specifications: 1x 12V Power USB Connector
- General Specifications: 1x 4 pin Power Din Connector
- General Specifications: 1x LP4 Connector
- General Specifications: 1x Internal USB Connector
- General Specifications: 4x Jumper Connectors
- Bracket Type: Standard Profile
- OS Support: Windows 2000/ME/2003/XP/Vista

