

12 ft 12V to M Barrel+USB Powered USB Cable - Plus Power

StarTech ID: PUSBMYB12V12



This 12ft 12V to M Barrel+USB Powered USB Cable features one 12v Powered USB Connector as well as one M Barrel+USB Connector, providing a durable 12ft connection for Powered USB devices.

Providing both USB data and USB device power through a single cable, Powered USB technology is emerging as the industry standard in a broad range of environments including retail POS, industrial, security and medical, based on true plug-and-play connectivity.

StarTech.com's versatile line of powered USB cables offers the high quality design and construction needed to usher in a new generation of USB connectivity, providing superb grounding and protection for all components as well as protection against the normal wear and tear that can result from repeated insertions and removals. This 12V to M Barrel+USB Powered USB Cable is backed by StarTech.com's Lifetime Warranty.

Applications and Solutions

- Connect POS scanners and printers to a PC for power and connectivity

Features

- Connect to your PC for Power and Data
- M Type Power Plug

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - 8 pin USB PlusPower (12 V) Male
- Cable Length: 12 ft [3.66 m]
- Connector B: 1 - USB B Male
- Connector B: 1 - M Type Barrel Center Positive - Power
- Color: Black
- Carton Quantity: 50
- Type and Rate: USB 2.0 - 480 Mbit/s
- Shipping (Package) Weight: 0.66 lb [0.3 kg]
- Cable Jacket Type: PVC - Polyvinyl Chloride

