

6 ft Standard Computer Power Cord - NEMA 5-15P to Right Angle C13

StarTech ID: PXT101L



This 6ft Right Angle Power Cord features a standard NEMA 5-15P connector as well as a right-angled C13 connector allowing you to plug a monitor, PC, or laser printer into a grounded power outlet.

The right angle C13 connector positions the shaft of the cable flush with the back of the device you are connecting, saving space at the connection point. Backed by Lifetime Warranty.

Applications and Solutions

- CSA approved
- Plugs monitor, PC, or laser printer into a grounded power outlet

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 120

- Shipping (Package) Weight: 0.4 lb [0.18 kg]
- Wire Gauge: 18 AWG
- Length: 6 ft., 1.8m
- Connectors: External Power Male, Computer Power Female
- General Specifications: EL302 (NEMA 5-15P) to EL702(IEC60320/C13) Right Angled
- General Specifications: 18/3 AWG, 60C, 10A, 125V, SVT

