

## 10 ft Standard Computer Power Cord - NEMA 5-15P to Right Angle C13

StarTech ID: PXT101L10



This 10ft Right Angle Power Cord features a standard NEMA 5-15P connector as well as a right-angled C13 connector allowing you to plug a monitor, PC, or laser printer into a grounded power outlet.

The right angle C13 connector positions the shaft of the cable flush with the back of the device you are connecting, saving space at the connection point. Backed by Lifetime Warranty.

### Applications

- Plugs monitor, PC, or laser printer into a grounded power outlet
- CSA approved

### Technical Specifications

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SVT
Connector A	1 - NEMA 5-15 Power (North America) Plug
Connector B	1 - IEC 60320 C13 Power
Color	Black
Wire Gauge	18 AWG
Cable Length	10 ft [3 m]
Product Length	10 ft [3 m]
Shipping (Package) Weight	0.6 lb [0.3 kg]

Certifications, Reports and Compatibility

