

1U 19" Rack Mount LCD Console - USB + PS/2

StarTech ID: RACKCONS1901



This 1U LCD KVM Rack Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space-efficient solution that provides total KVM control right from a server rack.

The KVM Rack Console integrates a 19in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable 1U design. When the rack console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget. Plus, the console supports connections to both PS/2 and USB controlled computers, accommodating both legacy and cutting edge computers.</p></div>
<div data-bbox="45 616 896 652" data-label="Text">
<p>To prevent unauthorized access, the 1U Rack Console can be locked closed, helping to reduce server room security concerns, while ensuring optimal control for authorized users.</p>
</div>
<div data-bbox="45 673 303 691" data-label="Section-Header">
<h3>Applications and Solutions</h3>
</div>
<div data-bbox="67 718 627 775" data-label="List-Group">

• Centralized control of dozens of PCs and servers if used with optional KVM
• Improving the internal space efficiency of existing cabinets
• Managing cabinet mounted servers

</div>
<div data-bbox="727 927 893 963" data-label="Page-Footer">
<p>www.StarTech.com
1-800-265-1844</p>
</div>

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Product Height: 1.72 in [43.8 mm]
- Product Length: 18.93 in [480.8 mm]
- OSD & Hotkey Support: Yes
- Carton Quantity: 1
- Shipping (Package) Weight: 41.86 lb [18.94 kg]
- Product Weight: 30.3 lb [13.71 kg]
- Product Width: 18.31 in [465 mm]
- Chassis Type: Heavy Duty Steel
- Supported Platforms: Both USB and PS/2
- Number of KVM Ports: 1
- Maximum Number of Users: 1
- Maximum Analog Resolutions: 1280x1024(SXGA)@60Hz
- Display Size: 19"
- Panel Type: Active Matrix TFT LCD
- Contrast Ratio: 500:1
- Color Depth: 24-bit, 16.7M colors (Truecolor)
- Pixel Pitch Support: Supports 0.098mm x 0.294mm
- Viewing Angle: Right-Left view 140 (Typ) & Up-Down View 140 (Typ)
- Response Time: 11ms
- Host Interface(s): 1 - High Density DB15 (VGA) Female
- Host Interface(s): 2 - 6 pin mini-DIN PS/2 Female
- Host Interface(s): 1 - USB A Female
- Input Voltage: 115 ~ 230 AC

- Center Tip Polarity: Positive
- Maximum Mounting Depth:: 39.37 in [1000 mm]
- Minimum Mounting Depth:: 21.81 in [554 mm]
- Operating Temperature: 0°C to 50°C (32°F to 122°F)
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- MTBF: 60,000 Hours

