

1U 19" Rackmount LCD Console - USB + PS/2

StarTech ID: RACKCONS1901



The RACKCONS1901 1U 19" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Centralized control of dozens of PCs and servers if used with optional KVM
- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Technical Specifications

Warranty	2 Years
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Key Lock	Yes
Host Connectors	1 - USB A (4 pin) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Host Connectors	2 - PS/2 (6 pin; Mini-DIN) Female
Brightness	250 cd/m ²
Contrast Ratio	1000:1
Pixel Pitch Support	0.294 x 0.294 mm
Response Time	5ms
Viewing Angle	176° (H), 170° (V)
IP Control	No
Maximum Analog Resolutions	1280x1024(SXGA)@60Hz
Aspect Ratio	Standard (4:3)
Color Depth	24-bit, 16.7M colors (Truecolor)
Maximum Number of Users	1
Port Selection Support	Hotkeys and OSD (On Screen Display)
MTBF	60,000 Hours
Maximum Mounting Depth	31.5 in [800 mm]
Minimum Mounting Depth	21.9 in [555 mm]
Product Height	1.8 in [45 mm]
Product Length	22.6 in [575 mm]
Product Weight	30.3 lb [13.7 kg]
Product Width	18.9 in [480.8 mm]
Color	Black
Enclosure Type	Heavy Duty Steel
Input Voltage	115 ~ 230 AC

Center Tip Polarity	Positive
Operating Temperature	05/10/2012eg;C to 505/10/2012eg;C (325/10/2012eg;F to 1225/10/2012eg;F)
Storage Temperature	-205/10/2012eg;C to 605/10/2012eg;C (-45/10/2012eg;F to 1405/10/2012eg;F)
Shipping (Package) Weight	41.9 lb [18.9 kg]
Included in Package	1 - 1U LCD Rack Console Drawer
Included in Package	1 - Mounting Rails - Set
Included in Package	1 - Console Cable Kit
Included in Package	1 - Power Cord

Certifications, Reports and Compatibility

