

**Refurbished 12U 19in Hinged Wall Mount Server Rack Cabinet w/ Steel Mesh Door**  
*StarTech ID: RK1219WALHMR*



This refurbished 19in Wall Mounted Rack (hinged, 12U) offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle. The sturdy 12U rack features a high quality steel design and a vented, tempered glass door to help keep your rack mount equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack accommodates 19" wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

### **Applications and Solutions**

- Mounting standard 19 in. networking equipment in exposed or unsecure locations

## Features

- Unique hinged design swings open for easy access to a your equipment
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Steel mesh door for added security
- Sturdy steel design

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Shipping (Package) Weight: 68.51 lb [31 kg]
- Key Lock: Yes
- Weight Capacity: 132.6 lb [60 kg]
- Frame Type: : Steel
- Front Door Type: : Steel Mesh
- Side Panel Type: : Solid Steel
- External Height : 25 in [635 mm]
- External Width : 23.62 in [600 mm]
- External Depth : 21.65 in [550 mm]
- Carton Quantity: 1
- Maximum Mounting Depth:: 16.25 in [412.75 mm]
- U Height: 12
- Industry Standards: EIA RS310-C
- Product Weight: 65.2 lb [29.5 kg]

