

12U 19in Wall Mounted Server Rack Cabinet

StarTech ID: RK1219WALL



This 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door to keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Applications and Solutions

- Mounting standard 19 in. networking equipment in exposed or insecure locations

Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Tempered, vented, lockable glass front door

Technical Specifications

- Warranty: Lifetime warranty
- Color: Beige
- Key Lock: Yes
- Weight Capacity: 132.6 lb [60 kg]
- Frame Type: : Steel
- Front Door Type: : Steel with Glass Window
- Side Panel Type: : Solid Steel
- External Height : 25.98 in [660 mm]
- External Width : 24.61 in [625 mm]
- External Depth : 24.8 in [630 mm]
- Internal Depth:: 22.5 in [571.5 mm]
- U Height: 12
- Product Weight: 66.3 lb [30 kg]
- Shipping (Package) Weight: 68.51 lb [31 kg]
- Carton Quantity: 1
- Maximum Mounting Depth:: 16.25 in [412.75 mm]

