

12U 19in Wall Mounted Server Rack Cabinet

StarTech ID: *RK1219WALL*



This 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door to keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations

Features

- Sturdy steel design
- Cable pass-through at rear of cabinet
- Tempered, vented, lockable glass front door
- Fan mounts for optional additional cooling
- Removable side panels with lock.

Technical Specifications

Warranty	Lifetime
U Height	12U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel w/ Window
Side Panel Type	Solid Steel
Key Lock	Yes
Fan(s)	Optional
Weight Capacity	132.6 lb [60 kg]
Color	Beige
Internal Width	18.3 in [465 mm]
Internal Depth	22.5 in [571.5 mm]
External Width	23.6 in [600 mm]
External Height	25 in [635 mm]
External Depth	23.6 in [600 mm]
Product Weight	66.3 lb [30 kg]
Maximum Mounting Depth	16.2 in [412.8 mm]
Flat Pack	No
Shipping (Package) Weight	68.5 lb [31 kg]
Included in Package	1 - 12U Server Cabinet
Included in Package	1 - Set of Keys

Certifications, Reports and Compatibility

