

## Refurbished 12U 19in Wall Mount Server Rack Cabinet w/ Steel Mesh Door

StarTech ID: RK1219WALLMR



This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door to keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

### Applications and Solutions

- Audio/Visual control centers
- Data centers
- Industrial control centers
- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Telecommunication closets

## Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Steel mesh door for added security
- Sturdy steel design

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Shipping (Package) Weight: 68.51 lb [31 kg]
- Key Lock: Yes
- Weight Capacity: 132.6 lb [60 kg]
- Frame Type: : Steel
- Front Door Type: : Steel Mesh
- Side Panel Type: : Solid Steel
- External Height : 25.98 in [660 mm]
- External Width : 24.61 in [625 mm]
- External Depth : 24.8 in [630 mm]
- Internal Depth:: 22.5 in [571.5 mm]
- U Height: 12
- Product Weight: 66.3 lb [30 kg]
- Carton Quantity: 1
- Maximum Mounting Depth:: 16.25 in [412.75 mm]
- Industry Standards: EIA RS310-C

