

Refurbished 12U 19in Wall Mount Server Rack Cabinet w/ Steel Mesh Door

StarTech ID: RK1219WALLMR



This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door to keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

Applications

- Audio/Visual control centers
- Data centers
- Industrial control centers
- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Telecommunication closets

Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Steel mesh door for added security

Technical Specifications

Warranty	0 Years
U Height	12U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel Mesh
Side Panel Type	Solid Steel
Key Lock	Yes
Industry Standards	EIA RS310-C
Fan(s)	Optional
Weight Capacity	132.6 lb [60 kg]
Color	Black
Internal Depth	22.5 in [571.5 mm]
External Width	24.6 in [625 mm]
External Height	26 in [660 mm]
External Depth	24.8 in [630 mm]
Product Weight	66.3 lb [30 kg]
Maximum Mounting Depth	16.2 in [412.8 mm]
Flat Pack	No
Shipping (Package) Weight	68.5 lb [31 kg]
Included in Package	1 - 19in Cabinet
Included in Package	1 - Package of Cab screws and Cage Nuts
Included in Package	1 - Keys

Certifications, Reports and Compatibility

