

Refurbished 12U 19in Wall Mounted Server Rack Cabinet

StarTech ID: RK1219WALLR



Refurbished cabinets may have minor scratches and dents similar to photos.

This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door keep your equipment safe and cool. Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Applications and Solutions

- Audio/Visual control centers
- Data centers
- Industrial control centers
- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Telecommunication closets

Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Tempered, vented, lockable glass front door

Technical Specifications

- Warranty: Lifetime warranty
- Color: Beige
- Shipping (Package) Weight: 68.51 lb [31 kg]
- Key Lock: Yes
- Weight Capacity: 132.6 lb [60 kg]
- Frame Type: : Steel
- Front Door Type: : Steel with Glass Window
- Side Panel Type: : Solid Steel
- U Height: 12
- Carton Quantity: 1
- External Height : 25.98 in [660 mm]
- External Width : 24.61 in [625 mm]
- External Depth : 24.8 in [630 mm]
- Internal Depth:: 22.5 in [571.5 mm]
- Minimum Mounting Depth:: 16.25 in [412.8 mm]
- Product Weight: 66.3 lb [30 kg]

