

## Refurbished 12U 19in Wall Mounted Server Rack Cabinet

StarTech ID: RK1219WALLR



Refurbished cabinets may have minor scratches and dents similar to photos.

This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

### Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Data centers
- Industrial control centers
- Telecommunication closets
- Audio/Visual control centers

### Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Tempered, vented, lockable glass front door

## Technical Specifications

Warranty	0 Years
U Height	12U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel w/ Window
Side Panel Type	Solid Steel
Key Lock	Yes
Fan(s)	Optional
Weight Capacity	132.6 lb [60 kg]
Color	Beige
Internal Width	18.3 in [465 mm]
Internal Depth	22.5 in [571.5 mm]
External Width	23.6 in [600 mm]
External Height	25 in [635 mm]
External Depth	23.6 in [600 mm]
Product Weight	66.3 lb [30 kg]
Minimum Mounting Depth	16.3 in [412.8 mm]
Flat Pack	No
Shipping (Package) Weight	31000
Included in Package	1 - 19in Cabinet
Included in Package	1 - Keys
Included in Package	1 - Package of Cab screws and Cage Nuts

## Certifications, Reports and Compatibility

