

12U 19in Desktop Open Frame 2 Post Rack

StarTech ID: RK12OD



The RK12OD 12U 19in Desktop Open Frame 2 Post Rack provides the perfect mounting option for smaller Audio/Video and IT equipment where space is limited and a full sized cabinet is not required.

The 12U rack features a compact and lightweight free-standing design that is suitable for installation on or around your desk giving you easy access to the mounted equipment in your workspace. This lightweight 2 post rack is engineered to meet EIA rack mount standards and includes all required assembly/mounting hardware making it a complete racking solution.

Backed by a StarTech.com lifetime warranty.

Applications

- Mount patch panels, network switches, and routers in small or home office networks or IT offices to provide easy access to equipment
- Mount KVMs and rack-mount computer/server systems neatly on or beside your desk
- Mount AV equipment such as broadcast/distribution devices, switches or extenders

Features

- Includes all the accessories required to mount hardware into the rack
- Easy to assemble
- Lightweight design for easy relocation
- Meets EIA standards

Technical Specifications

Warranty	Lifetime
U Height	12U
Frame Type	Open Frame
Wallmountable	No
Front Door Type	Open
Industry Standards	EIA RS310-C
Fan(s)	No
Weight Capacity	110.5 lb [50 kg]
Color	Black
Internal Width	17.8 in [451 mm]
External Width	19.8 in [504 mm]
External Height	23 in [584.4 mm]
External Depth	11.5 in [292 mm]
Flat Pack	Yes
Shipping (Package) Weight	6.7 lb [3 kg]
Included in Package	2 - 12U Vertical Post
Included in Package	2 - Legs
Included in Package	1 - Package of assembly hardware (8 Screws)
Included in Package	20 - M5 Screws, and Cage Nuts
Included in Package	4 - Rubber Feet

Certifications, Reports and Compatibility

