

36in Sliding Server Rack Cabinet Shelf

StarTech ID: RK36SLFS



The RK36SLFS 36in Sliding Server Rack Cabinet Shelf is designed for the StarTech.com RK4236BK series of cabinets, or can be installed in virtually any industry standard 36in depth 19" rack that supports side mounting options.

This 36in Sliding Server Rack Shelf offers a vented design for increased airflow, and is constructed out of cold-rolled steel, offering a weight capacity of up to 45 lbs (20 kg). Perfect for keeping testing equipment, laptop computers, documents and other tools at arm's reach, while the sturdy sliding rails provide smooth and easy access.

Backed by a StarTech.com 2-year warranty.

Applications

- Store equipment in racks with a sliding form factor for easy access
- For use with 19" wide, 36" depth server racks and cabinets
- Supply additional storage space for mission critical hardware

Features

- Slats preserve airflow inside the rack
- Cold-rolled steel construction
- Weight capacity of up to 45 lbs (20 kg)

Technical Specifications

Warranty	2 Years
U Height	1U
Mounting Options	Side Mount (Front and Rear)
Weight Capacity	44.2 lb [20 kg]
External Depth	25.6 in [650 mm]
Product Length	25.6 in [650 mm]
Product Width	18.5 in [470 mm]
Product Height	1.9 in [4.8 cm]
Shipping (Package) Weight	12 lb [5.5 kg]
Included in Package	1 - 36" deep sliding shelf
Included in Package	1 - Mounting hardware

Certifications, Reports and Compatibility

