

42U 42in Server Rack Cabinet (no Sides)

StarTech ID: RK4242BKNS



The RK4242BKNS 42U 42in Server Rack Cabinet (No Sides) features an all steel, welded frame construction that provides durable, high quality rack storage at an affordable price.

This modular 42U cabinet helps save space in the server room by using an innovative split rear door, and is designed to suit any server room footprint design, while housing any standard 19in rackmount equipment. To simplify planning and equipment installation, the rack includes an integrated cable management system and clearly marked rail spacing. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

The RK4242BKNS is also available as an enclosed rack (RK4242BK) so that several cabinets can be joined together using only 2 side panels, saving cost and increasing passive airflow.

Backed by a StarTech.com Lifetime Warranty.

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Extra deep 42" enclosure accommodates all full size rackmount equipment
- Lockable front and rear doors
- Split rear door minimizes the required access space behind the cabinet
- Front and rear doors are easily removable and can be reversed
- Includes integrated cable management system
- All steel, welded frame construction
- Ships fully assembled

Technical Specifications

| | |
|---------------------------|----------------------------------------|
| Warranty | Lifetime |
| Casters | Included |
| U Height | 42U |
| Frame Type | Enclosed Cabinet |
| Wallmountable | No |
| Front Door Type | Steel Mesh |
| Back Door Type | Steel Mesh |
| Key Lock | Yes |
| Industry Standards | EIA RS310-D |
| Fan(s) | No |
| Weight Capacity | 2210 lb [1000 kg] |
| Color | Black |
| Internal Width | 18.3 in [465 mm] |
| Internal Depth | 34 in [863.6 mm] |
| External Width | 23.8 in [605 mm] |
| External Height | 77.5 in [1968 mm] |
| External Depth | 42.1 in [1070 mm] |
| Product Weight | 221 lb [100 kg] |
| Height with Casters | 78.7 in [1998 mm] |
| Flat Pack | No |
| Shipping (Package) Weight | 245.3 lb [111 kg] |
| Included in Package | 1 - 42U 42" DuraRak Rack |
| Included in Package | 1 - Integrated cable management system |
| Included in Package | 4 - Leveling feet |
| Included in Package | 4 - Cable access caps |
| Included in Package | 1 - Allen key for skid removal |
| Included in Package | 1 - Set of keys for doors |
| Included in Package | 1 - Package of mounting screws |

Certifications, Reports and Compatibility

