

43U 19in Knock Down Audio Video Rack

StarTech ID: RK4320AV



This high quality 43U 19in Knock Down AV Rack is designed to provide A/V professionals and integrators with a high-quality solution for housing audio-video equipment.

The AV rack provides 43U of cabinet space and accommodates AV components measuring up to 19in wide by 20in deep. Featuring 3mm steel rails and a highly durable design, the AV Rack features an impressive 400lb. storage capacity and provides optimized ventilation as well as easy access to cables and components.

Applications

- Designed to provide A/V professionals and integrators with a high-quality solution for housing audio/video equipment
- Keep equipment secure and stored properly with the Converge A/V rack

Features

- Innovative bolt-together assembly
- 1/2" & 3/4" Conduit Knock Outs for simple cable configuration
- 19" Width provides broad compatibility with standard A/V component sizes
- 3.0 millimeter threaded 10-32 front and rear rack rails
- 20" depth to fit most A/V components
- Solid construction allows for a maximum capacity of 400 lbs
- Provides optimized ventilation as well as easy access to cables and components
- Provides maximum durability and versatility

Technical Specifications

Warranty	2 Years
Casters	Optional
U Height	43U
Frame Type	Open Frame
Wallmountable	No
Front Door Type	Open
Industry Standards	EIA RS310-C
Weight Capacity	400 lb [181 kg]
Color	Black
Internal Width	17.7 in [450.9 mm]
Internal Height	75.1 in [1908.2 mm]
External Width	19.2 in [488.9 mm]
External Height	78.7 in [2000.3 mm]
External Depth	19.7 in [501.6 mm]
Minimum Mounting Depth	19.7 in [501.6 mm]
Height with Casters	81.6 in [2073.3 mm]
Flat Pack	Yes
Shipping (Package) Weight	54.2 lb [24.5 kg]

Certifications, Reports and Compatibility

