

Refurbished 1U 17" Rack Mount LCD Console - USB + PS/2

StarTech ID: RKCONS1701R



The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1701R offers a single port KVM integrated module, has an eye-catching 17-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1701R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

Applications and Solutions

- Centralized control of dozens of PCs and servers if used with optional KVM
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Technical Specifications

- Color: Black
- Shipping (Package) Weight: 38.08 lb [17.23 kg]
- Chassis Type: Heavy Duty Steel
- Supported Platforms: PS/2
- Number of KVM Ports: 1
- Cascadable: Yes
- Maximum Analog Resolutions: 1280x1024 @ 60Hz
- OSD & Hotkey Support: Yes
- Display Size: 17"
- Panel Type: Active Matrix TFT LCD
- Contrast Ratio: 450:1
- Color Depth: 24-bit, 16.7M colors (Truecolor)
- Pixel Pitch Support: 0.264mm x 0.264mm
- Viewing Angle: Right-Left view 60 ~ 70 (Typ) & Up-Down View 45 ~ 60(Typ)
- Response Time: 11ms
- Host Interface(s): 2 - 6 pin mini-DIN PS/2 Female
- Host Interface(s): 1 - High Density DB15 (VGA) Female
- Power Adapter Included: Yes
- Input Voltage: 115 ~ 230 AC
- Minimum Mounting Depth:: 30 in [762 mm]
- Product Length: 18.93 in [480.8 mm]
- Product Width: 18.31 in [465 mm]
- Product Height: 1.72 in [43.8 mm]
- Product Weight: 423.6 oz [12000 g]
- Operating Temperature: 0 ~ 50 °C / 32 ~ 122 °F

- Storage Temperature: 20 ~ 60 °C / -4 ~ 140 °F
- Carton Quantity: 1

