

Refurbished DuraView 17" Folding LCD Rack Console with 8 Port Multi-Platform KVM StarTech ID: RKCONS1708R



The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1708R offers an 8 Port KVM module, has an eye-catching 17-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1708R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. The product is capable of managing up to 64 servers through eight cascaded 8-port KVMs. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

Applications and Solutions

- Centralized control of up to 64 PCs
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers
- User can complete the basic tasks in the server room

Features

- Auto Scan Mode lets you switch between computers for easy monitoring
- Cascadable design
- Compatible with PC, Mac and Sun servers and systems
- Durable design
- Hot-pluggable
- Login authentication restricts access to authorized users
- On Screen Display (OSD)
- Security features, including port locking and auto scan
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 8 port KVM switch Module controls up to 8 computers directly and up to 64 computers by cascading 8 additional KVM switches

Technical Specifications

- Color: Black
- Maximum Cascaded Computers: 64
- Maximum Analog Resolutions: 1280x1024 @85Hz (SXGA)
- OSD & Hotkey Support: Both hotkeys and OSD (On Screen Display)
- Power Adapter Included: Yes
- Power Adapter - Amperage: 4A
- Power Adapter - DC Voltage: 12V
- Carton Quantity: 1
- Shipping (Package) Weight: 44.51 lb [20.14 kg]
- Chassis Type: Heavy Duty Steel
- Supported Platforms: Both USB and PS/2
- Number of KVM Ports: 8
- Maximum Number of Users: 1
- Cascadable: Yes
- Display Size: 17"
- Panel Type: Active Matrix TFT LCD
- Contrast Ratio: 450:1
- Color Depth: 32-bit
- Pixel Pitch Support: 0.264mm x 0.264mm
- Viewing Angle: Right-Left view 60~70 (Typ)

Up-Down View 45~60 (Typ)

- Response Time: 14ms
- Console Interface(s): 1 - 36 pin Centronics Female
- Console Interface(s): 2 - 6 pin mini-DIN PS/2 Female
- Console Interface(s): 1 - High Density DB15 (VGA) Female
- Host Interface(s): 8 - High Density DB15 (VGA) Female
- Input Voltage: 115 ~ 230 AC
- Output Voltage: 12 DC
- Output Current: 4000mA
- Center Tip Polarity: Positive
- Minimum Mounting Depth:: 30 in [762 mm]
- Product Length: 18.5 in [470 mm]
- Product Width: 17.32 in [440 mm]

- Product Height: 1.73 in [44 mm]
- Product Weight: 24.31 lb [11 kg]
- Operating Temperature: 0 – 50 °C / 32 – 122 °F
- Storage Temperature: -20 – 60 °C / -4 -140 °F
- Humidity: 10%~90%RH

