

## Refurbished DuraView 17" Folding LCD Rack Console with 8 Port Multi-Platform KVM

StarTech ID: RKCONS1708R



Refurbished units may have minor scratches or dents.

The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1708R offers an 8 Port KVM module, has an eye-catching 17-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1708R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. The product is capable of managing up to 64 servers through eight cascaded 8-port KVMs. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

### Applications

- Centralized control of up to 64 PCs
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers
- User can complete the basic tasks in the server room

## Features

- Auto Scan Mode lets you switch between computers for easy monitoring
- Cascadable design
- Compatible with PC, Mac and Sun servers and systems
- Durable design
- Hot-pluggable
- Login authentication restricts access to authorized users
- On Screen Display (OSD)
- Security features, including port locking and auto scan
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 8 port KVM switch Module controls up to 8 computers directly and up to 64 computers by cascading 8 additional KVM switches

**Technical Specifications**

Warranty	0 Years
Key Lock	Yes
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	8
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Daisy-Chain	Yes
Console Interface(s)	1 - Centronics (36 pin) Male
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	8 - VGA (15 pin; High Density D-Sub) Female
Brightness	250 cd/m <sup>2</sup>
Contrast Ratio	1000:1
Pixel Pitch Support	0.264 x 0.264 mm
Response Time	5ms
Viewing Angle	170° (H), 160° (V)
IP Control	No
Maximum Analog Resolutions	1280x1024 @85Hz (SXGA)
Aspect Ratio	Standard (4:3)
Color Depth	32-bit
Maximum Number of Users	1
Maximum Cascaded Computers	64
Port Selection Support	Hotkeys and OSD (On Screen Display)
Maximum Mounting Depth	
Minimum Mounting Depth	30 in [762 mm]
Product Height	1.7 in [44 mm]
Product Length	18.5 in [470 mm]
Product Weight	24.3 lb [11 kg]
Product Width	17.3 in [440 mm]
Color	Black

Enclosure Type	Heavy Duty Steel
Power Adapter Included	Yes
Input Voltage	115 ~ 230 AC
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive
Operating Temperature	0 – 50 °C / 32 – 122 °F
Storage Temperature	-20 – 60 °C / -4 -140 °F
Humidity	10%~90%RH
Shipping (Package) Weight	20140
Included in Package	1 - 1U LCD Rack Console Drawer
Included in Package	1 - 1U 8 Port Multi-Platform KVM Switch
Included in Package	1 - Mounting Rails (Set)
Included in Package	1 - Power Adapter

**Certifications, Reports and Compatibility**

