

Refurbished 1U DuraView 19" Folding LCD KVM Rack Console

StarTech ID: RKCONS1901R



The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1901R offers a single port KVM integrated module, has an eye-catching 19-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1901R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

Applications

- Centralized control of dozens of PCs and servers if used with optional KVM
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Technical Specifications

Warranty	0 Years
Key Lock	Yes
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Daisy-Chain	Yes
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Host Connectors	2 - PS/2 (6 pin; Mini-DIN) Female
Brightness	250 cd/m ²
Contrast Ratio	1000:1
Pixel Pitch Support	0.294 x 0.294 mm
Response Time	5ms
Viewing Angle	176° (H), 170° (V)
IP Control	No
Maximum Analog Resolutions	1280x1024 @85Hz (SXGA)
Aspect Ratio	Standard (4:3)
Color Depth	32-bit
Maximum Number of Users	1
Port Selection Support	Hotkeys and OSD (On Screen Display)
Maximum Mounting Depth	31.5 in [800 mm]
Minimum Mounting Depth	21.9 in [555 mm]
Product Height	1.8 in [45 mm]
Product Length	22.6 in [575 mm]
Product Weight	24.3 lb [11 kg]
Product Width	18.9 in [480.8 mm]
Color	Black
Enclosure Type	Heavy Duty Steel
Power Adapter Included	Yes
Input Voltage	115 ~ 230 AC

Operating Temperature	0 – 50 5/8/2012eg;C / 32 – 122 5/8/2012eg;F
Storage Temperature	-20 – 60 5/8/2012eg;C / -4 – 122 5/8/2012eg;F
Humidity	10%~90%RH
Shipping (Package) Weight	20140
Included in Package	1 - 1U LCD Rack Console Drawer
Included in Package	1 - Mounting Rails - Set
Included in Package	1 - Console Cable Kit
Included in Package	1 - Power Cord

Certifications, Reports and Compatibility

