

## Refurbished DuraView 19" Folding LCD Rack Console with 16 Port Multi-Platform KVM StarTech ID: RKCONS1916R



The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1916R offers a 16 Port KVM module, has an eye-catching 19-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1916R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. The product is capable of managing up to 136 servers through eight cascaded 16-port KVMs. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

### Applications and Solutions

- Centralized control of up to 136 Servers
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

## **Features**

- Auto Scan Mode lets you switch between computers for easy monitoring
- Cascadable design
- Compatible with PC, Mac and Sun servers and systems
- Durable design
- Hot-pluggable
- Login authentication restricts access to authorized users
- On Screen Display (OSD)
- Security features, including port locking and auto scan
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 16 port KVM switch Module controls up to 16 computers directly and up to 136 computers by cascading 8 additional KVM switches

## Technical Specifications

- Color: Black
- Shipping (Package) Weight: 46.37 lb [20.98 kg]
- Chassis Type: Heavy Duty Steel
- Supported Platforms: PS/2, USB, and SUN
- Number of KVM Ports: 16
- Maximum Number of Users: 1
- Cascadable: Yes
- Maximum Cascaded Computers: 136
- Maximum Analog Resolutions: 1280x1024(SXGA)@60Hz
- OSD & Hotkey Support: Yes
- Display Size: 19"
- Panel Type: Active Matrix TFT LCD
- Contrast Ratio: 500:1
- Color Depth: 24-bit, 16.7M colors (Truecolor)
- Pixel Pitch Support: 0.264 mm x 0.264 mm
- Viewing Angle: Right-Left view 60 ~ 70 (Typ) & Up-Down View 45 ~ 60(Typ)
- Response Time: 11ms
- Console Interface(s): 1 - 36 pin Centronics Male
- Console Interface(s): 2 - 6 pin mini-DIN PS/2 Female
- Console Interface(s): 1 - High Density DB15 (VGA) Female
- Host Interface(s): 16 - High Density DB15 (VGA) Female
- Power Adapter Included: Yes
- Input Voltage: 115 ~ 230 AC
- Output Voltage: 12 DC
- Output Current: 4000 mA
- Center Tip Polarity: Positive
- Plug Type: M
- Minimum Mounting Depth:: 30 in [762 mm]
- Product Length: 20.87 in [530 mm]
- Product Width: 17.32 in [440 mm]
- Product Height: 1.73 in [44 mm]
- Product Weight: 423.6 oz [12000 g]
- Operating Temperature: 0 ~ 50 °C / 32 ~ 122 °F

- Storage Temperature: 20 ~ 60 °C / -4 ~ 140 °F
- Humidity: 10%~90%RH
- Carton Quantity: 1

