

## Refurbished DuraView 19" Folding LCD Rack Console with 16 Port Multi-Platform KVM

StarTech ID: RKCONS1916R



Refurbished units may have minor scratches or dents.

The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1916R offers a 16 Port KVM module, has an eye-catching 19-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1916R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. The product is capable of managing up to 136 servers through eight cascaded 16-port KVMs. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

### Applications

- Centralized control of up to 136 Servers
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

## Features

- Auto Scan Mode lets you switch between computers for easy monitoring
- Cascadable design
- Compatible with PC, Mac and Sun servers and systems
- Durable design
- Hot-pluggable
- Login authentication restricts access to authorized users
- On Screen Display (OSD)
- Security features, including port locking and auto scan
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 16 port KVM switch Module controls up to 16 computers directly and up to 136 computers by cascading 8 additional KVM switches

**Technical Specifications**

Warranty	0 Years
Key Lock	Yes
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	16
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Daisy-Chain	Yes
Console Interface(s)	1 - Centronics (36 pin) Female
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	16 - VGA (15 pin; High Density D-Sub) Female
Brightness	250 cd/m <sup>2</sup>
Contrast Ratio	1000:1
Pixel Pitch Support	0.294 x 0.294 mm
Response Time	5ms
Viewing Angle	176° (H), 170° (V)
IP Control	No
Maximum Analog Resolutions	1280x1024(SXGA)@60Hz
Aspect Ratio	Standard (4:3)
Color Depth	24-bit, 16.7M colors (Truecolor)
Maximum Number of Users	1
Maximum Cascaded Computers	136
Port Selection Support	Hotkeys and OSD (On Screen Display)
Maximum Mounting Depth	
Minimum Mounting Depth	30 in [762 mm]
Product Height	1.7 in [44 mm]
Product Length	20.9 in [530 mm]
Product Weight	26.5 lb [12 kg]
Product Width	17.3 in [440 mm]
Color	Black

Enclosure Type	Heavy Duty Steel
Power Adapter Included	Yes
Input Voltage	115 ~ 230 AC
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Operating Temperature	0 ~ 50 °C / 32 ~ 122 °F
Storage Temperature	20 ~ 60 °C / -4 ~ 140 °F
Humidity	10%~90%RH
Shipping (Package) Weight	20980
Included in Package	1 - 1U LCD Rack Console Drawer
Included in Package	1 - 1U 16 Port Multi-Platform KVM Switch
Included in Package	1 - Mounting Rails (Set)
Included in Package	1 - Power Adapter

**Certifications, Reports and Compatibility**

