

## 24 Outlet 120V 15A Rackmount Power Strip

StarTech ID: *RKPW247015*



This 24 outlet rackmount power strip provides a 0U solution for your rackmount equipment and fits most 42U racks and equipment cabinets. The 10ft power cord provides plenty of reach to power outlets, and the 24 evenly spaced outlets help keep power cabling clean and efficiently routed.

### Features

- Provides 24 (120V 15A) power outlets
- Mounts vertically, taking up 0U of rack space
- 10 ft (3 m) power cord

## Technical Specifications

Warranty	Lifetime
Output Connectors	1 - NEMA 5-15 Power (North America) Plug
Output Connectors	24 - NEMA 5-15 Power (North America) Receptacle
Maximum Input Current per Phase	15A
Maximum Total Current Draw per Phase	15A
Regulatory Derated Input Current (North America)	12A
Nominal Input Voltage	120V
Nominal Output Voltage	120V
Maximum Output Voltage	125V
Color	Black
Cable Length	10 ft [3 m]
Product Length	1.5 in [38 mm]
Product Width	1 in [25 mm]
Product Height	72 in [1830 mm]
Product Weight	6.6 lb [3 kg]
Shipping (Package) Weight	5.8 lb [2.6 kg]

## Certifications, Reports and Compatibility

