

Black 4U Steel Rackmount Server Case

StarTech ID: RMC4000I



This rugged 4U Rackmount Server Case features a 1mm steel chassis that lets you keep your rackmounted industrial PCs or servers protected from dust and damage while allowing superior airflow to ensure reliable, stable operation even in harsh industrial environments.

Providing a reliable 12cm front fan and a lockable front panel door, this 4U Server case can accommodate up to two additional 60mm fans in the rear of the chassis, providing not only a solid platform from which to build your server or rackmount PC, but also a scalable cooling solution that ensures you can maintain necessary operating temperatures in any environment.

Applications

- Industrial workstation PCs
- Industrial automation control PCs
- Industrial servers

Features

- Rugged 1mm SECC steel construction
- Full front panel lockable protective door
- 120mm front fan with air filter provides plenty of clean air circulation. Can accommodate up to two additional 60mm fans in rear.
- Adjustable I/O card holders prevent cards from becoming unseated in their slots
- Temperature and fan failure LEDs warn of possible impending system failure

Technical Specifications

Warranty	2 Years
Number of external 3.5 inch bays	1
Number of internal 3.5 inch bays	1
Number of external 5.25 inch bays	3
Fans	1 - 120 mm
General Specifications	2 screws
General Specifications	Full Front Lockable
General Specifications	Washable foam
Color	Black
Product Length	18.5 in [470 mm]
Product Width	19 in [483 mm]
Product Height	7 in [177 mm]
Product Weight	37.6 lb [17 kg]
LED Indicators	1 - Fan failure warning
LED Indicators	1 - Hard drive activity
LED Indicators	1 - Power
LED Indicators	1 - Temperature warning
Shipping (Package) Weight	26.6 lb [12 kg]

Certifications, Reports and Compatibility

