

2.5in USB SATA External Hard Drive Enclosure w/ Integrated USB cable

StarTech ID: SAT2510SCB



The SAT2510SCB External Hard Drive Enclosure transforms any 2.5" SATA (SATA, SATA II, SATA III) hard drive or solid state drive (SSD) into a portable USB external hard drive.

Designed to provide convenience and portability, the hard drive enclosure features a built-on USB 2.0 cable and a durable yet lightweight aluminum construction that fits perfectly in your pocket or laptop bag when not in use.

To simplify connection to the host desktop or laptop computer, the enclosure can be powered through its built-on USB connection, eliminating the need for an external power supply and having to find a suitable power outlet while making it easier to backup data or load stored files.

Applications and Solutions

- Backup important data to an external storage device
- Share large files between computers quickly and securely without a network
- Busy travelers who can't waste time locating or sorting out cables while on the road
- Add-on extra storage to almost any USB enabled computer system
- Create a fast, portable external storage solution for desktops, laptops or netbooks

- Retrieve data from old SATA drive, or turn the unused drive into additional external storage space

Features

- Powered directly from the USB port
- High Speed USB 2.0 host interface, with supported transfer rates up to 480 Mbps
- Power/Activity LED indicator
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) or solid state drives (SSD)
- Integrated 2in (5cm) USB cable
- Light-weight and durable aluminum chassis
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

- Warranty: 2 Years
- Chipset ID: SunplusIT - SPIF301
- Max Drive Capacity: Tested up to 500 GB
- Product Height: 0.63 in [16 mm]
- Humidity: 10 to 90% RH
- LED Indicators: 1 - Blue Power and Activity
- Product Length: 5.16 in [131 mm]
- Max Drive Height: 0.37 in [9.5 mm]
- Operating Temperature: 0°C to 70°C (32°F to 158°F)
- Output Current: 500mA
- Carton Quantity: 20
- Storage Temperature: -20°C to 75°C (-4°F to 167°F)
- Shipping (Package) Weight: 9.88 oz [280 g]
- Product Weight: 5.12 oz [145 g]
- Product Width: 3.31 in [84 mm]

