

## 2.5in SATA External Hard Drive Enclosure w/ 3.5/5.25 Front Drive Bay

StarTech ID: SAT2510U2REM



This 2.5in SATA External Hard Drive Enclosure lets you turn any 2.5in Serial ATA hard drive (HDD) or solid state drive (SSD) into a dual purpose, internal removable hard drive.

Perfect for large volume data offloads, digital video recording, surveillance, audio editing (no fan so noiseless), external storage, or a simple way to swap storage between your notebook and desktop computers, the external hard drive enclosure is easy to install and use. Simply install the provided drive bracket & bay into any 5.25in or 3.5in drive bay on the host computer and connect the bay to the computer SATA port. Then, install the 2.5in SATA hard drive in the external enclosure, and insert the enclosure into the 5.25in/3.5in bay for instant connectivity with the host computer!

The hard drive enclosure is ejectable, and supports standalone installation, letting you connect the enclosure to any computer through a USB 2.0 port. The enclosure supports high capacity drives in a 9.5mm height form factor.

For even more versatility, StarTech.com offers [Extra 2.5in SATA Hard Drive Enclosures for the SAT2510U2REM](#), providing multiple enclosures that can be swapped in and out of the main computer.

### Applications and Solutions

- Professionals working with large files who need to transport them between computers/locations
- Easily work on and store large presentations or demos from your desktop, then transport it to a clients location without having to transfer files between drives
- Business professionals who need first hand access to their office data while traveling
- Users who need both fast internal storage and portable external storage

## Features

- Frontmount drive bay installs into any standard 3.5" or 5.25" bay
- Unique enclosure design allows it to be used as an internal removable drive or as a regular external enclosure
- Push button drive ejection from the frontmount bay
- Durable aluminum construction for the drive enclosure
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible

## Technical Specifications

- Warranty: 2 Years
- Chipset ID: JMicron JM20336
- Max Drive Capacity: 500GB
- Product Height: 1.57 in [40 mm]
- Product Length: 5.43 in [138 mm]
- Maximum Data Transfer Rate: 3Gbps Internal (SATA II)

480Mbps External (USB 2.0)

- Max Drive Height: 0.37 in [9.5 mm]
- OS Compatibility: Windows ME/2000/XP/Vista; MAC OS 9.x or Higher; Linux 2.4.1.0 and Above
- Carton Quantity: 10
- Shipping (Package) Weight: 1.61 lb [0.73 kg]
- Product Weight: 1.1 lb [0.5 kg]
- Product Width: 5.67 in [144 mm]
- 2.5" Enclosure Dim.: 131 x 77 x 14mm (LxWxH)

