

Extra 2.5in SATA Hard Drive Enclosure for SAT2510U2REM

StarTech ID: SAT2510U2S



This spare 2.5in removable SATA drive enclosure is designed for use with StarTech.com's [3.5in Bay Removable 2.5in SATA Drive Enclosure](#) (SAT2510U2REM), providing additional external storage via USB 2.0, and in turn allowing multiple users to share and access files from a single desktop system.

The spare drive enclosure features a portable design that adds to the mobility of your data, making it convenient to access your files externally from a desktop or laptop computer, or to migrate data to similarly equipped desktops in another office, data center or home environment.

Applications

- Use multiple hard drives with the same SAT2510U2REM installation for different scenarios/configurations or rotating backup disks
- Professionals working with large files who need to transport them between computers/locations
- Easily work on and store large presentations or demos from your desktop, then transport it to a clients location without having to transfer files between drives
- Business professionals who need first hand access to their office data while travelling
- Users who need both fast internal storage and portable external storage

Features

- Extra/replacement removable drive enclosure for SAT2510U2REM
- Unique enclosure design allows it to be used as an internal removable drive or as a regular external enclosure
- Powered directly from the USB port, when used externally
- Light-weight and durable aluminum construction for the drive enclosure
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Interface	USB 2.0
Number of Drives	1
Drive Size	2.5in
Drive Type	SATA
Drive Installation	Removable
Fan(s)	No
Chipset ID	JMicron - JM20336
Connector Type(s)	1 - SATA Power (15 pin) Plug
Connector Type(s)	1 - USB B (4 pin) Male
Drive Connectors	1 - SATA Data & Power Combo (7+15 pin) Receptacle
Host Connectors	1 - SATA Data & Power Combo (7+15 pin) Plug
Host Connectors	1 - USB Mini-B (5 pin) Female
Type and Rate	USB 2.0 - 480 Mbit/s
Type and Rate	SATA II (3 Gbps)
RAID	No
Max Drive Capacity	Tested up to 500 GB
OS Compatibility	Windows ME/2000/XP/Vista; MAC OS 9.x or Higher; Linux 2.4.1.0 and Above
Color	Silver
Enclosure Type	Aluminum and Plastic
Max Drive Height	0.4 in [9.5 mm]
Product Length	5.2 in [133 mm]
Product Width	3.1 in [79 mm]
Product Height	0.6 in [15 mm]
Product Weight	3.5 oz [100 g]
Note	This is an extra 2.5" hard drive enclosure for the SAT2510U2REM
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - Hard Drive Enclosure
Included in Package	1 - USB Cable
Included in Package	1 - Screw Kit

Certifications, Reports and Compatibility

