

5.25in Bay Removable 3.5in SATA HDD Enclosure

StarTech ID: SAT3510U2REM



This USB to SATA External Hard Drive Enclosure turns a 3.5in SATA (SATA, SATA II, SATA III) hard drive into a dual purpose add-on external storage and internal removable hard drive storage solution!

Supporting the latest generation of Serial ATA hard drives, this external hard drive enclosure is the ideal solution for large volume data offloads, digital video recording, surveillance systems, audio editing (no fan so noiseless), external storage, or a simple way to swap storage between your laptop and desktop computers.

Simply install the provided bay enclosure bracket into any 5.25in drive bay on the host computer, and enjoy the convenience of removable storage that can be ejected from one computer and connected to another as a conventional external hard drive.

Applications and Solutions

- Professionals working with large files who need to transport them between computers/locations without a network
- Easily work on and store large presentations or demos from your desktop, then transport it to a clients location without having to transfer files between drives
- Business professionals who need first hand access to their office data while traveling
- Users who need both fast internal storage and portable external storage

Features

- Front mount drive bay installs into any standard 5.25" bay
- Unique enclosure design allows it to be used as an internal removable SATA drive or as a regular external USB enclosure
- Push lever drive ejection from the front mount bay
- Durable aluminum construction for the drive enclosure chassis
- Power/Activity LED indicator
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

- Warranty: 2 Years
- Product Height: 1.26 in [32 mm]
- LED Indicators: 1 - Power and activity
- Product Length: 7.8 in [198 mm]
- OS Compatibility: Windows ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 9.x and up
- Power Adapter - Amperage: 2.0A
- Power Adapter - DC Voltage: 12V/5V
- Carton Quantity: 6
- Shipping (Package) Weight: 2.96 lb [1.34 kg]
- Product Weight: 17.65 oz [500 g]
- Product Width: 4.45 in [113 mm]
- Connectors:
 - Drive: 1x SATA Data 7 Pin Female
 - 1x SATA Power 15 Pin Female
 - Host: 1x SATA Data 7 Pin Male
 - 1x LP4 Male
 - 1x USB B Female (External)
- Internal Transfer Rate: 3 Gbps via SATA
- External Transfer Rate: 480 Mbps via USB

- System Requirements:
- Internal: 1x 5.25" bay & SATA support
- External: Any available USB port
- Supported Drives: 3.5" SATA (SATA, SATA II, SATA III) hard drives tested up to 2.0 TB in size

