

3.5in 4 Drive eSATA USB Multi Bay External Hard Drive Enclosure

StarTech ID: SAT3540U2E



StarTech.com's SAT3540U2E Multi Bay External Hard Drive Enclosure is a high-performance 4-drive SATA enclosure connected to host systems through eSATA and/or USB. The enclosure can be connected to two systems simultaneously, one through USB and one through eSATA, allowing users to share installed SATA hard drives between the computers by switching host connections back and forth at the touch of a button.

The 4-drive SATA enclosure works with high capacity 3.5in Serial ATA hard drives (SATA, SATA II, SATA III) and features a removable front cover that ensures easy access while installing or removing the drives.

Applications and Solutions

- Add external storage solution without worrying about driver or software support
- External storage that is easily transferable between different computer systems
- Large volume external storage for backups/archiving
- Video editing or photography professional/enthusiasts working with very large file sizes

Features

- High Speed USB 2.0 host interface, with transfer rates up to 480Mbps
- SATA revision 2 compliant eSATA host interface with transfer rates up to 3.0Gbps
- Manually switchable between eSATA and USB host interfaces
- Removable front cover and accessible drive trays
- 80mm cooling fan with 4 selectable speeds: Low, Med, High, Auto
- Auto power saving when host connection disconnected or turned off
- LED status indicators for each drive, host interface and fan speed
- No driver or software installation
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and hot-swap compatible
- Rugged aluminum chassis

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Max Drive Capacity: 2.0 TeraBytes x 4 Drives - Total 8 TeraBytes
- Drive Connectors: 2 - 7 pin SATA DATA Female
- Drive Connectors: 2 - 15 pin SATA Power Female
- Enclosure Type: Aluminum
- Fan Bearing Type: Ball Bearing
- Product Height: 6.69 in [170 mm]
- Host Connectors: 1 - USB B Female
- Host Connectors: 1 - 7 pin eSATA DATA Female
- Humidity: 90%RH
- Input Voltage: 115 ~ 230 AC
- LED Indicators: 3 - Fan speed indicators
- LED Indicators: 2 - Fan mode indicators
- LED Indicators: 2 - Interface indicators
- LED Indicators: 1 - Power indicator (Blue - On, Orange - Standby, Off - Off)
- LED Indicators: 1 - Sync mode indicator (Blue - 6 second delay after disconnect to turn off, Orange - Standby right after disconnect, Off - Do nothing on disconnect)
- Product Length: 8.46 in [215 mm]
- Fans: 1 - 80 mm
- Operating Temperature: -20°C to 60°C (-4°F to 140°F)
- Output Current: 5000mA
- Output Voltage: 12 DC
- Power Adapter Included: Yes
- Carton Quantity: 4
- RPM: Low - 1200rpm
Med - 1800rpm
High - 2500rpm
- Storage Temperature: -25°C to 70°C (-13°F to 158°F)
- Shipping (Package) Weight: 6.94 lb [3.14 kg]
- Product Weight: 3.98 lb [1.8 kg]
- Product Width: 4.96 in [126 mm]
- Number of Drives: 4

- Compatible Drives : 3.5" SATA
- Chipset ID: EXAR - XRS10L240
- Type and Rate: SATA 3 Gbit/s (SATA II)
- Type and Rate: USB 2.0 - 480 Mbit/s

