

36in SATA to Right Angle SATA Serial ATA Cable

StarTech ID: SATA36RA1



The SATA36RA1 right angle SATA cable features a standard (straight) female Serial ATA connector as well as a right-angled (female) SATA connector, providing a simple 36-inch connection to a Serial ATA drive, even if space near the drive SATA port is limited.

Once the right-angled SATA connector has been inserted into the SATA data port on the drive, the shaft of the cable is seated flush with the rear panel of the drive, eliminating the clutter of excess cable at the connection point - an ideal solution for small or micro form factor computer cases.

The right angled SATA cable features a thin, narrow construction that helps to improve airflow within the computer case; the cable also features a rugged, yet flexible design that makes it easy to make the SATA connection as needed, and is backed by StarTech.com's Lifetime Warranty.

Applications

- Connecting SATA Drive Arrays
- Compatible with Serial ATA Hard Drives, CD-RW, DVDs, and other devices
- For use in servers and storage
- High-end workstations
- Mini tower computers

Features

- Compliant with Serial ATA III Specifications
- Supports fast data transfer rates of up to 6 Gbps
- Meets current Serial ATA specifications and ensures maximum performance
- Offers 36" in length for greater flexibility
- Specially designed to improve system airflow and routability

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	1 - SATA (7 pin; Data) Receptacle
Connector B	1 - SATA (7 pin; Data) Receptacle
Type and Rate	SATA III (6 Gbps)
Color	Red
Connector Style	Straight to Right Angle
Cable Length	36 in [914.4 mm]
Shipping (Package) Weight	0 lb [0 kg]
Included in Package	1 - 36in SATA to Right Angle SATA Serial ATA Cable

Certifications, Reports and Compatibility

