

## eSATA USB to SATA External Hard Drive Docking Station for 2.5 or 3.5in

StarTech ID: SATADOCKU2E



This eSATA/USB to SATA External HDD Dock Adapter provides immediate, swappable access to any 2.5in or 3.5in SATA (SATA, SATA II, SATA III) hard drive (HDD) or solid state drive (SSD) - without having to mount the hard drive, or install it in an enclosure! Large capacity drives (tested with up to 4TB 3.5" and 1TB 2.5" drives) can be used to greatly enhance your computer's storage/backup capabilities.

Simply connect this docking station to a computer using either eSATA or USB 2.0, and it's as simple as inserting your 2.5in or 3.5in SATA hard drive into the dock whenever needed.

A perfect solution for data recovery, drive imaging, and testing centers, or any environment that requires fast access to uninstalled/archived drives, the SATA HDD Dock supports plug and play installation on most operating systems. Plus, the HDD docking station supports data transfer speeds of up to 1.5 Gbps (using eSATA) and 480Mbps (using USB 2.0) between host and dock - ensuring effortless data dumps, backups and hassle-free file transfers. Double the value of this hard drive docking station, using a [SATA to IDE hard drive adapter](#) (SAT2IDEADP), which enables you to use any 2.5 or 3.5in IDE hard drive in a SATA hard drive dock slot.

### Applications

- Access spare or removed 2.5/3.5" drives quickly to retrieve data from
- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Technicians who regularly test or benchmark different hard drives

## Features

- Top slot loading design with drive doors
- Power/Activity LED indicator
- SATA revision 1 compliant eSATA host interfaces, with support for transfer rates up to 1.5 Gbps
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Compact desktop style form factor

Technical Specifications

Warranty	2 Years
Interface	USB 2.0 & eSATA
Number of Drives	1
Drive Size	2.5in & 3.5in
Drive Type	SATA
Fan(s)	No
Drive Connectors	1 - SATA Data & Power Combo (7+15 pin) Receptacle
Host Connectors	1 - eSATA (7 pin; Data) Plug
Host Connectors	1 - USB B (4 pin) Female
Type and Rate	USB 2.0 - 480 Mbit/s
Type and Rate	SATA I (1.5 Gbps)
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM 3.5" hard drives and 1TB 5400 RPM 2.5" hard drive
Insertion Rating	15,000 Cycles
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ 2003(32/64bit)/ VISTA (32/64bit)/ 7(32/64bit), Mac OS G4 10.0 and up, G5 10.3.9+, and Linux
Color	Black
Enclosure Type	Plastic
Product Length	5.5 in [140 mm]
Product Width	3.6 in [91 mm]
Product Height	2.2 in [55 mm]
Product Weight	7.8 oz [221 g]
LED Indicators	1 - Solid - Power, Blinking - Activity
Shipping (Package) Weight	1.9 lb [0.8 kg]
Included in Package	1 - SATA hard drive docking station
Included in Package	1 - eSATA Cable
Included in Package	1 - USB Cable
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

