

36in Right Angle SATA Cable

StarTech ID: SATARA36



This 3ft right angle Serial ATA cable guarantees you'll be able to plug in your high-performance SATA hard drives no matter how tight your space is, using right angled SATA connectors that reduce the amount of space required at the connection point.

Featuring a narrow yet durable construction, and right angled SATA data connectors on both ends of the cable, these flexible cables improve airflow and reduce clutter in your case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and durability, this right angled SATA cable is backed by our lifetime warranty.

Applications

- For use in servers and storage subsystems
- High-end workstations
- ATA Drive Arrays
- Mini tower computers
- Compatible with Serial ATA Hard Drives, CD-RW, DVDs, and other devices

Features

- Specially designed to improve system airflow and rout ability
- Meets current Serial ATA specifications and ensures maximum performance and reliability
- Fast data transfer rate of up to 6 Gbps
- Offers 36 inches in length for greater flexibility
- Compliant with Serial ATA III Specifications

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	1 - SATA (7 pin; Data) Receptacle
Connector B	1 - SATA (7 pin; Data) Receptacle
Type and Rate	SATA III (6 Gbps)
Color	Red
Cable Length	36 in [914.4 mm]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 36in Right Angle SATA Cable

Certifications, Reports and Compatibility

